

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Incandescent

# P350133-009

## Glass Domes

A classic three-light 15in semi-flush fixture with dome shaped etched glass, solid trim and decorative knob. The Brushed Nickel finish complements a variety of interior settings, such as Modern, Traditional and Farmhouse.

- The classic ceiling fixture: A perfect dome with metallic rim and finials
- The domes are crafted from etched glass and come in flush-mount and semi-flush varieties
- Close-to-ceiling lights like this semi-flush convertible are natural choices for closets, hallways and other small rooms
- They are good choices to brighten an entire room – ideal for ambient or general illumination
- The contoured, simple design makes it a fit across most styles, including Modern, Traditional and Farmhouse
- Brushed Nickel finish puts the focus on the light's milky white glass dome
- Measures 15in diameter x 11in ht.
- Includes ceiling-mount and hanging hardware
- Uses three 75-watt max. medium base lamps or LED equivalent (sold separately)
- Compatible with standard wall dimmer
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available



**Width: 15"**  
**Height: 11"**  
**Overall Ht. W/Chain: 49"**

Width: 14-15/16"  
Height: 4-3/4"

**Category:** Close-to-Ceiling

**Finish:** Brushed Nickel (plated)

**Construction:** Steel Construction

**Glass/Shade:** Etched glass Bowl

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Flush-Mount mounted Mounting plate for outlet box included Three feet of 9 gauge chain supplied Canopy covers a standard 4" octagonal recessed outlet box 4.875" W., 1.125" ht., 4.875" depth	Pre-wired 10 feet of wire supplied 120 V	Quantity: Three 75w max. Medium Base E26 base porcelain sockets	cULus Dry location listed 1 year warranty