

DATE:	TYPE:	
NAME:		
PROJECT:		

Incandescent

## P350142-081

## Point Dume™ - Sequit Point

The romance and architectural presence of a lighthouse is expressed in the Sequit Point group. In the same way strips of glass increased the effectiveness of lighthouse beacons, the modern Sequit Point series benefits from a similar ingenuity. Mercury glass sleeves stand in tandem with clear glass rods and an Antique Nickel finish to provide a familiar glow for the convertible ceiling fixture/ pendant. This family of fixtures is part of Point Dume™ lighting collection which celebrates a curated mix of yesterday and today, distilling both industrial and artisanal influences.

Category: Close-to-Ceiling
Finish: Antique Nickel (plated)
Construction: Steel Construction
Glass/Shade: Mercury glass Cylindrical



Diameter: 14" Height: 9-5/8" Depth: 14-3/8"

Overall Ht. W/Stem: 78"

Glass

Height: 8-1/2" Glass 2 Width: 0-3/8" Length: 0-3/8" Height: 8-1/2"

Width: 9-13/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem mounted	Pre-wired	Quantity:	cETLus Dry location listed
Mounting plate for outlet box included  Six links of 9 gauge chain supplied  One 6", four 12" lengths of stem included  Canopy covers a standard 4" octagonal recessed outlet box  5.125" W., 0.8125" ht., 5.125" depth	10 feet of wire supplied 120 V	Three 60w max. Candelabra Base E12 base Phenolic sockets	1 year warranty