

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P350154-141 Austelle

Your home will exude comfort and sophistication with the graceful Austelle Collection's Two-Light Galvanized Flush Mount. A breathtaking mesh shade takes center stage as juxtaposed galvanized light sockets peek from within the shade's embrace. Incorporate clear light bulbs for a pinch of contemporary shine or opt for vintage bulbs to enhance the light fixture's antique demeanor.

- Breathtaking mesh shade takes center stage enhancing the light fixture's rustic demeanor.
- Juxtaposed galvanized light sockets peek from within the shade's embrace.
- Incorporate clear light bulbs for a pinch of contemporary shine or opt for vintage bulbs for an antique glow.
- Ideal for any foyer, dining room, hallway, or kitchen.
- A graceful choice for bohemian, coastal, modern, or transitional interiors.
- Measures 14-inch width by 6-1/2-inch height.
- Uses two candelabra base bulbs that are sold separately (60w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Close-to-Ceiling

Finish: Galvanized Finish (Painted)

Construction: Steel Construction



Diameter: 14 in
Height: 6-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	Prewired	Quantity:	CETLus Damp Location Listed
Mounting plate for outlet box included	6 inches of wire supplied	Two 60 W max. Medium Base or LED equivalent	1-year Limited Warranty
Ceiling Pan covers a standard 4" recessed outlet box: 9.75" W., 1" ht., 9.75" depth	120 V	E26 base Porcelain sockets	