

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

**P350226-31M**  
**Singleton**

**Category:** Close-to-Ceiling  
**Finish:** Matte Black (Painted)  
**Construction:** Steel Construction  
**Glass/Shade:** Clear Glass Bowl



Diameter: 7-5/8 in  
Height: 7 in

Clear Glass Bowl  
Width: 7-5/8 in  
Height: 4-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Semi-Flush	6 inches of wire supplied	(1) Medium Base (E26) Socket	cCSAus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5" W., 0.812" ht., 5" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	