

Project:			
Fixture Type:			
Location:			
Contact:			

# LED Bulkheads

Wall or ceiling mounted • Wet location listed PROGRESS LED



### **Description:**

One-Light 6-1/2" LED Wall or Ceiling Bulkhead. General purpose LED luminaire comprised of a diecast aluminum frame and polycarbonate diffuser. Fixtures are impact resistant and can be mounted on wall or ceiling. Replaceable LED module. Black finish.

## P3647-3130K9

#### Images:

### **Specifications:**

- Black (-31) (powder coat paint)
- Aluminum Construction
- Frosted polycarbonate diffuser
- LED Module is replaceable (part # 93054049)
- · Robust and energy efficient.
- Offers various mounting options.
- · Can be widely adapted for indoor and outdoor applications.
- Meets California Title 24 high efficacy requirements for outdoor use only.
- 623 lumens 69.2 lumens/watt per module (source)
- · 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Unit covers a standard 4" octagonal recessed outlet box
- Mounting plate for outlet box included
- · 6" of wire supplied
- · ENERGY STAR® qualified
- · Meets California Title 24 high efficacy requirements for outdoor use only



## Performance:

Number of Modules	1		
Input Power	9w		
Input Voltage	120 V		
Input Frequency	60 Hz		
Lumens/LPW (Source)	623/69.2 (LM-82)		
Lumens/LPW (Delivered)	488/62.1656050955414 (LM-79)		
CCT	3000 K		
CRI	90 CRI		
Life (hours)	60,000 (L70/TM-21)		
FCC	Meets FCC Title 47, Part 15 Class B		
Min. Start Temp	-30 °C		
Max. Operating Temp	30 °C		
Warranty	5 year warranty		
Labels	cCSAus Wet location listed		
	ENERGY STAR® qualified		
	Meets California Title 24 high efficacy requirements		
	for outdoor use only		

#### **Dimensions:**

Width: 6-1/2" Depth: 4-3/8" Height: 10-1/2" H/CTR: 5-1/4"

Glass

Width: 3-7/16" Length: 6-1/8" Height: 10-1/4"



# LED Bulkheads

Wall or ceiling mounted • Wet location listed PROGRESS LED



## P3647-3130K9

## **Dimming Notes:**

P3647 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## **Dimming Controls**

Lutron Nova T NTELV-300

Lutron Vierti VTELV-600

Lutron Ariadni AYCL-153P

Lutron Diva DVCL-153P

Lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Leviton Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.