

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P3690-20

Flat Glass

Two-light foyer fixture with clear, flat glass panels and ivory candle clusters.

- Antique Bronze finish.
- Clear flat glass panels.
- White candle clusters.

Category: Hall & Foyer

Finish: Antique Bronze (painted)

Construction: Steel Construction

Glass/Shade: Clear flat glass



Diameter: 9-7/16"
Height: 12"
CTC: 10-7/8"
Overall Ht. W/Chain: 49"

Width: 5-7/8"
Height: 6-9/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain/ctc mounted Mounting bracket for outlet box included Three feet of 9 gauge chain supplied Canopy covers a standard 4" octagonal recessed outlet box 5.5" W.	Pre-wired 15 feet of wire supplied 120 V	Quantity: Two 60w max. Candelabra Base E12 base phenolic sockets	UL-CUL Dry location listed 1 year warranty