

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Compact fluorescent

P3761-09EBWB

Melon

One-light flush mount with etched ribbed glass and bold solid trims with ribbed accents. Twist on and off glass bowl. 13 watt GU24 spiral compact fluorescent lamps included.

- Brushed Nickel finish.
- Etched ribbed glass.
- Twist on and off glass bowl.
- Meets California Title 24.

Category: Close-to-Ceiling

Finish: Brushed Nickel (Plated)

Construction: Steel Construction

Glass/Shade: Etched faceted glass bowl



Diameter: 11-1/2"

Height: 4-1/8"

Glass

Width: 8-3/4"

Height: 3-1/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
<p>Ceiling flush mounted</p> <p>Mounting strap for outlet box included</p> <p>Ceiling pan covers a standard 4" octagonal recessed outlet box</p> <p>11.5" W., 1.625" depth</p>	<p>Pre-wired</p> <p>6" of wire supplied</p> <p>120 V</p>	<p>Quantity:</p> <p>One 13w max. GU-24(included)</p> <p>GU24 base sockets</p>	<p>UL-CUL Damp location listed</p> <p>1 year warranty</p> <p>Meets California Title 24 high efficacy requirements</p>