

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Compact fluorescent

# P3765-09EBWB

## Melon

Two-light flush mount with alabaster glass with etched detailing completed by ribbed trimming. Twist on and off glass bowl. 13 watt GU24 spiral compact fluorescent lamps included.

- Two-light flush mount.
- Alabaster Glass Bowl.
- Twist on and off glass bowl.
- Meets California Title 24.

**Category:** Close-to-Ceiling

**Finish:** Brushed Nickel (Plated)

**Construction:** Steel Construction

**Glass/Shade:** Etched Alabaster glass bowl



**Diameter: 14"**  
**Height: 4-3/4"**

Glass  
Width: 10-7/8"  
Height: 4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling flush mounted  Mounting strap for outlet box included  Ceiling pan covers a standard 4" octagonal recessed outlet box  14" W.	Pre-wired  6" of wire supplied  120 V	Quantity:  Two 13w max. GU-24(included)  GU24 base sockets	cCSAus Damp location listed  1 year warranty  Meets California Title 24 high efficacy requirements