

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Compact fluorescent

P3765-20EBWB

Melon

Two-light flush mount with alabaster glass bowl. Twist on and off glass bowl. 13 watt GU24 spiral compact fluorescent lamps included.

- Two-light flush mount.
- Alabaster Glass Bowl.
- 13 watt GU24 spiral compact fluorescent lamps.
- Meets California Title 24.

Category: Close-to-Ceiling

Finish: Antique Bronze (Painted)

Construction: Steel Construction

Glass/Shade: Etched Alabaster glass bowl



Diameter: 14"

Height: 4-3/4"

Glass

Width: 10-7/8"

Height: 4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling flush mounted Mounting strap for outlet box included Ceiling pan covers a standard 4" octagonal recessed outlet box 14" W.	Pre-wired 6" of wire supplied 120 V	Quantity: Two 13w max. GU-24(included) GU24 base sockets	cCSAus Damp location listed 1 year warranty Meets California Title 24 high efficacy requirements