

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P3855-20

Joy

Two-light semi-flush with modern trumpet glass shade in a simple yet elegant soft etched tea-stained finish. This collection delivers a minimalist urban style with Antique Bronze finish.

- Antique Bronze finish.
- Modern trumpet glass.
- Minimalist urban style.

Category: Close-to-Ceiling

Finish: Antique Bronze (painted)

Construction: Steel Construction

Glass/Shade: Tea-stained glass cone shaped bowl



Diameter: 13-5/16"
Height: 9-9/16"

Glass
Width: 13-5/16"
Height: 5-1/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling semi-flush mounted Mounting strap for outlet box included Canopy covers a standard 4" octagonal recessed outlet box 4.75" W., 1.1875" ht., 4.75" depth	Pre-wired 6" of wire supplied 120 V	Quantity: Two 100w max. Medium Base E26 base ceramic sockets	cCSAus Damp location listed 1 year warranty