

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Compact fluorescent

# P3925-09EB

## Dome Glass CTC CFL

Two-light energy efficient flush mount with dome shaped alabaster glass, solid trim and decorative knobs. Center lock-up with matching finial. Brushed Nickel finish.

- Brushed Nickel finish.
- Alabaster Glass.
- Decorative details.
- Meets California Title 24.

**Category:** Close-to-Ceiling

**Finish:** Brushed Nickel (plated)

**Construction:** Steel Construction

**Glass/Shade:** Alabaster glass bowl



**Diameter:** 13-1/4"  
**Height:** 5-11/16"

**Glass**  
**Width:** 9-13/16"  
**Height:** 3-9/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling flush mounted Mounting strap for outlet box included Ceiling pan covers a standard 4" octagonal recessed outlet box 13.1875" W., 1.375" ht., 13.1875" depth	Pre-wired 6" of wire supplied 120 V	Quantity: Two 18w max. GU-24 GU24 base sockets	cCSAus Damp location listed 1 year warranty Meets California Title 24 high efficacy requirements