

DATE:

NAME:

PROJECT:

Incandescent

## P400054-015

TYPE:

## Topsail

Topsail features a graceful curving frame paired with elegant parchment-finish glass shades to create a clean, modern form. Classic metal fittings enhance the crisp appearance of a brilliant Polished Chrome finish. This collection provides the perfect complement to coastal-inspired or casual décor.

- Features a graceful curving frame
- Elegant parchment-finish glass shades create a clean, modern form
- Classic metal fittings enhance the crisp appearance of a brilliant Polished Chrome finish
- The perfect complement to coastal-inspired or casual décor

## Category: Chandeliers

Finish: Polished Chrome (plated) Construction: Steel construction Glass/Shade: Etched Parchment glass shades



Diameter: 30" Height: 25-3/8" Overall Ht. W/Chain: 147"

Glass Width: 5-3/16" Height: 5-5/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Pre-wired	Quantity:	cULus Dry location listed
Mounting strap for outlet box included Ten feet of 9 gauge chain supplied covers a standard 4" octagonal recessed outlet box	15 feet of wire supplied 120 V	Nine 100w max. Medium Base E26 base socket	