

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P400073-020

Tilley

Rustic and vintage décor is a popular trend that can transform a home into a nostalgic retreat. Tilley features warehouse style shades formed from metal mesh that merge with a faux-painted, wooden rim for an artful yet industrial style.

- Rustic and vintage décor is a popular trend that can transform a home into a nostalgic retreat
- Tilley features warehouse style shades formed from metal mesh
- Features popular Antique Bronze finish
- A hand painted, faux wooden rim evokes an artful, yet industrial, style
- Uses three 100-watt max. medium base lamps (sold separately)
- Versatile fixture that enhances rustic farmhouse, modern farmhouse, urban industrial and coastal styles
- Ideal for welcoming guests and visitors in a foyer or entryway, as well as in dining room or living room settings

Category: Chandeliers

Finish: Antique Bronze (painted)

Construction: Steel construction shade



Diameter: 20"
Height: 15-1/4"
Overall Ht. W/Chain: 90-1/2"

Glass
Width: 6-5/8"
Height: 4-1/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Hanging mounted Mounting strap for outlet box included Six feet of 9 gauge chain supplied Canopy covers a standard 4" octagonal recessed outlet box 5.125" W., 0.75" ht., 5.125" depth	15 feet of wire supplied 120 V	Quantity: Three 100w max. medium E26 base	cULus Dry location listed 1 year limited warranty