

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400096-009

Kene

Add a modern romance to the heart of your home with this lovely chandelier. Quiet etched glass diffusers are surrounded by clear outer glass shades for a soft, luxurious touch. The shades sit on an elegant brushed nickel frame with gently flowing arms.

- Quiet etched glass diffusers are surrounded by clear outer glass shades for a soft, luxurious touch.
- The shades sit on an elegant brushed nickel frame with gently flowing arms.
- Add a modern romance to the heart of your home with this lovely chandelier.
- Ideal for any foyer, kitchen, or dining room.
- Perfect for modern, Craftsman, or contemporary settings.
- Measures 32-3/4-inch width by 29-7/8-inch height.
- Uses nine medium base bulbs that is sold separately (100w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Chandeliers

Finish: Brushed Nickel (Plated)

Construction: Steel Construction

Glass/Shade: Clear glass Cylindrical Shade, Etched Glass Cylindrical Shade



Diameter: 32-3/4 in
Height: 29-7/8 in
Overall Ht. W/Chain: 152-1/2 in

Clear glass Cylindrical Shade
Width: 4-3/4 in
Height: 5-9/16 in

Etched Glass Cylindrical Shade
Width: 2-15/16 in
Height: 4-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity: Nine 75 W max. Medium Base or LED equivalent	CULus Dry Location Listed
1/4 IP mounting plate for outlet box included	15 feet of wire supplied	E26 base Porcelain sockets	1-year Limited Warranty
10 feet of 9 gauge chain supplied	120 V		
Canopy covers a standard 4" recessed outlet box: 5.125" W., 1.1875" ht., 5.125" depth			