

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Incandescent

# P400160-009

## Stratham

With a glamorous and modern appeal, the Stratham Collection's five-light chandelier features a sparkling string of cylindrical drops and a stunning, faceted K9 glass column. Opulent accent finials complete well-executed design to add dimension and overall depth for modern, luxury homes.

- A modern execution of the traditional chandelier form
- Swags of crystal beads are draped from curving metallic arms on this five-light chandelier
- A faceted glass column and luxe finials complete the design
- The chandelier makes a beautiful welcoming statement in an entry foyer, works well paired over a dining table, and completes the look for a sophisticated master bedroom.
- Stratham finds an ideal home in Modern and Luxe environments
- Top with a white fabric shade (P8704-01) for a classic look
- Brushed Nickel finish is a sleek foil to the crystal and glass accents
- Measures 27 1/4in diameter x 25 1/2in ht.
- Overall height with chain is 101in
- Uses five, 60-watt max. candelabra base bulbs including LED equivalent (sold separately)
- Compatible with standard wall dimmer
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available



**Diameter: 27-1/4"**  
**Height: 25-1/2"**  
**Overall Ht. W/Chain: 101"**

**Category:** Chandeliers

**Finish:** Brushed Nickel (plated)

**Construction:** Steel Construction

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted Mounting strap for outlet box included Six feet of 9 gauge chain supplied Canopy covers a standard 4" octagonal recessed outlet box 5.625" W., 0.875" ht., 5.625" depth	Pre-wired 15 feet of wire supplied 120 V	Quantity: Five 60w max. Candelabra Base E12 base phenolic sockets	cULus Dry location listed 1 year warranty