

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400218-031

Durrell

This versatile chandelier from the Durrell Collection will easily find a home in a variety of settings in need of generous illumination. A sailcloth linen shade creates a soft, muted glow. Inside the shade nestle light bases on gently curved arms coated in a beautiful black finish. A wooden stem coated in a ceruse black finish attaches the light fixture to a linked chain.

- Sailcloth linen shade creates a soft, muted glow.
- Inside the shade nestle light bases on gently curved arms coated in a beautiful black finish.
- A wooden stem coated in a ceruse black finish attaches the light fixture to a linked chain.
- Ideal for any foyer, hallway, dining room, or kitchen.
- Perfect for rustic, farmhouse, and coastal settings.
- Measures 21-inch width by 22-1/2-inch height.
- Uses four candelabra base bulbs that are sold separately (60w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Chandeliers

Finish: Matte Black (Painted)

Construction: Steel Construction

Glass/Shade: Sailcloth Linen Fabric drum shade



Diameter: 21 in
Height: 22-1/2 in
Overall Ht. W/Chain: 97-1/2 in

Sailcloth Linen Fabric drum shade
Width: 21 in
Height: 8-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity:	CULus Dry Location Listed
1/8 IP mounting plate for outlet box included	15 feet of wire supplied	Four 60 W max. Candelabra Base or LED equivalent	1-year Limited Warranty
6 feet of 9 gauge chain supplied	120 V	E12 base Phenolic sockets	
Canopy covers a standard 4" recessed outlet box: 5" W., 0.75" ht., 5" depth			