

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400225-031 Chadwick

Stick with simple geometric forms and clean crisp lines with the modern Chadwick Collection's Three-Light Matte Black Island Chandelier. A beautiful etched opal glass shade visually calms the sharp edges of the boxy frame in a masterful stroke of design excellence. The frame is coated in a matte black finish that visually contrasts with the light shade. The light fixture is just right for spaces in need of a subtle, feminine touch.

- A beautiful etched opal glass shade visually calms the sharp frame in a masterful stroke of design excellence.
- The frame is coated in a matte black finish that visually contrasts with the light shade.
- The island chandelier is just right for spaces in need of a subtle, feminine touch.
- Ideal for any foyer, dining room, or kitchen.
- Perfect for transitional, modern, and contemporary settings.
- Measures 40-inch width by 8-3/4-inch height.
- Uses three medium base bulbs that are sold separately (60w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Chandeliers

Finish: Matte Black (Painted)

Construction: Steel Construction

Glass/Shade: Etched Opal glass Cylindrical Shade



Width: 40 in
Height: 8-3/4 in
Depth: 12 in
Overall Ht. W/Stem: 59 in

Etched Opal glass Cylindrical Shade
Width: 4-5/16 in
Height: 6-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem hung with swivel mounted	Prewired	Quantity:	CULus Dry Location Listed
1/8 IP mounting plate for outlet box included	15 feet of wire supplied	Three 100 W max. Medium Base or LED equivalent	1-year Limited Warranty
Two 6", eight 12" lengths of stem included	120 V	E26 base Porcelain sockets	
Canopy covers a standard 4" recessed outlet box: 15.125" W., 0.75" ht., 4.5" depth			