

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400235-031

Stockbrace

Stockbrace Collection 3-Light Matte Black Clear Glass Farmhouse Chandelier Light

Category: Chandeliers
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear Glass Cone



Length: 16 in
 Diameter: 16 in
 Height: 18 in
 Overall Ht. W/Chain Or Stem: 84 in

Clear Glass Cone
 Width: 4-1/2 in
 Height: 6-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain	15 feet of wire supplied	Quantity: three 60 W max.	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 V	E26 base Porcelain Socket	1-year Limited Warranty
six links of 9 gauge chain supplied			
one 6", four 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 5" W., 0.75" ht., 5" depth			