

Spoke LED

Ceiling/Stem + Chain Mounted • Damp Location Listed **PROGRESS LED**

Description:

Spoke LED Collection 1-Light Brushed Nickel LED Modern Hanging Pendant Light

Specifications:

- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 5 in W., 2 in ht., 5 in depth
- Swivel mounting strap for outlet box included
- 120 in of wire supplied 54 in

Performance:

Number of Modules	1
Input Power	20 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	2,096/104 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed Meets California Title 24 JA8-2019

P400255-009-30



Dimensions:

Length: 25-1/2 in
Height: 27-1/8 in
Overall Ht. W/Chain And Stem: 67-3/16 in

P400255-009-30

Dimming Notes:

P400255-009-30 is designed to be compatible with many Triac/ELV controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

IDevices_IDEV009

Leviton_6674

Lutron_NTEVL-300

Lutron_DVELV-300P

Lutron_DVCL-253P

Lutron_Caseta Wireless

Lutron_TGCL-153-PH-WH

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.