

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400294-163

Elara

Elara Collection Six-Light New Traditional Vintage Brass Chandelier Light

Category: Chandeliers
Finish: Vintage Brass (Plated)
Construction: Steel Construction



Diameter: 30 in
Height: 10-3/8 in
Overall Ht. W/Stem: 65 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	10 feet of wire supplied	(6) Candelabra Base (E12) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
One 6", four 12" lengths of stem included		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.75" W., 1" ht., 5.75" depth		Fully dimmable with dimmable bulbs	