

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P400295-31M Parkhurst

Parkhurst Collection Three-Light New Traditional Matte Black Clear Glass Chandelier Light

**Category:** Chandeliers  
**Finish:** Matte Black (Painted)  
**Construction:** Steel Construction  
**Glass/Shade:** Clear Glass Bell



Diameter: 21 in  
Height: 12-1/4 in  
Overall Ht. W/Chain Or Stem: 78 in

Clear Glass Bell  
Width: 4-1/4 in  
Height: 5-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(3) Medium Base (E26) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Six links of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
One 6", four 12" lengths of stem included		Fully dimmable with dimmable bulbs	
Canopy covers a standard 4" recessed outlet box: 5.68" W., 1" ht., 5.68" depth			