

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400296-31M Parkhurst

Parkhurst Collection Five-Light New Traditional Matte Black Clear Glass Chandelier Light

Category: Chandeliers
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear Glass Bell



Diameter: 25-1/4 in
Height: 12-1/2 in
Overall Ht. W/Chain Or Stem: 78-1/2 in

Clear Glass Bell
Width: 4-1/4 in
Height: 5-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(5) Candelabra Base (E12) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
Six links of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
One 6", four 12" lengths of stem included		Fully dimmable with dimmable bulbs	
Canopy covers a standard 4" recessed outlet box: 5.68" W., 1" ht., 5.68" depth			