

Project:			
Fixture Type:			
Location:			
Contact			

## P400297-109

## **Parkhurst**

Parkhurst Collection Six-Light New Traditional Brushed Bronze Clear Glass Chandelier Light

Category: Chandeliers

Finish: Brushed Bronze (Plated)
Construction: Steel Construction
Glass/Shade: Clear Glass Bell



Diameter: 30 in Height: 14 in

Overall Ht. W/Chain Or Stem: 80 in

Clear Glass Bell Width: 4-1/4 in Height: 5-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(6) Candelabra Base (E12) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
Six links of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
One 6", four 12" lengths of stem included		Fully dimmable with dimmable bulbs	
Canopy covers a standard 4" recessed outlet box: 5.68" W., 1" ht., 5.68" depth			