progress lighting DESIGN**+SERIES**™

Project:			
Fixture Type:			
Location:			
Contact:			

P400299-009 Saffert

Saffert Collection Four-Light New Traditional Brushed Nickel Clear Glass Chandelier Light

Category: Chandeliers Finish: Brushed Nickel (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Bowl



Diameter: 29-3/8 in Height: 22-1/2 in Overall Ht. W/Stem: 78-1/2 in

Clear Glass Bowl Width: 7-1/2 in Height: 6-1/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	15 feet of wire supplied	(4) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
One 6", four 12" lengths of stem included		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 4.5" W., 0.812" ht., 4.5" depth		Fully dimmable with dimmable bulbs	