

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P4179-80

Santiago

Casual detail meets rustic design in the Santiago collection. Featuring spiraled detailing, scrolled arms, romantic Jasmine Mist glass and subtle forged iron twists. . Nine-light, two-tier chandelier.



Diameter: 32"
 Height: 29-1/4"
 Overall ht. w/chain: 104"

Category: Chandeliers

Finish: Forged Black (painted)

Construction: Steel construction

Glass: Jasmine mist glass shades

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted Mounting strap for outlet box included Six feet 9 gauge chain supplied Canopy covers a standard 4" hexagonal recessed outlet box	Pre-wired 15 feet of wire supplied 120V	Quantity: 9 60W Candelabra Base Candelabra phenolic sockets	UL-CUL Dry location listed 1 year warranty Companion fixtures are available