

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P4314-77

Kensington

The casual, comfortable feel of the Kensington Collection is perfect for many interiors. Twelve-light, three-tier chandelier features scrolled metalwork in a Forged Bronze finish. Trumpet-shaped, slightly textured glass shades are complemented by a frosted caramel swirl finish.

Category: Chandeliers

Finish: Forged Bronze (painted)

Construction: Steel construction construction

Glass: Frosted caramel swirl glass trumpet shaped shades



Diameter: 34"
Height: 41-7/8"
Overall ht. w/chain: 166"

Glass: 7" dia.
Height: 5-3/4"

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|---|---|--|---|
| Ceiling chain mounted Mounting strap for outlet box included Ten feet 9 gauge chain supplied Canopy covers a standard 4" hexagonal recessed outlet box | Pre-wired 15 feet of wire supplied 120V | Quantity: 12 100W Medium Base Medium ceramic sockets | UL-CUL Dry location listed 1 year warranty Companion Bath and Vanity, Ceiling Fans, Chandelier, Close-to-ceiling, Hall and Foyer, Pendant, Wall bracket, fixtures are available |