

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P4411-77

Fiorentino

Twelve-light, two-tier chandelier captures the romantic feel of a candlelit evening in a rustic Italian villa as champagne drip glass candles nest within sparkling seeded glass shades. Hand-painted Forged Bronze finish blends brown and black tones, and faint golden highlights. Combination of etched detailed columns and banding accent stylized leaves. Ten feet of 6 gauge chain is supplied for ceiling chain mount.

Category: Chandeliers

Finish: Forged Bronze (painted)

Construction: Steel construction

Glass: Clear seeded glass



Diameter: 32-7/8"

Height: 37-5/8"

Overall ht. w/chain: 160-9/16"

Glass: 6-3/8" dia.

Height: 6-1/2"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted Mounting strap for outlet box included Ten feet 6 gauge chain supplied Canopy covers a standard 4" hexagonal recessed outlet box 5-1/2" dia., 1-1/2" depth	Pre-wired 15 feet of wire supplied 120V	Quantity: 12 60W Candelabra Base Candelabra phenolic sockets	UL-CUL Dry location listed 1 year warranty Companion fixtures are available