

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

P500121-031

Seneca

The refined, Seneca four-light foyer will create its own conversation amongst guests as they experience its generous glow in an entryway or as they are entertained at a dining room table or kitchen island. Four smooth, Black-finished arms extend to hold the beautiful candelabra lights accented in painted antique nickel. With its remarkable balance of simplicity and elegance, the fixture is a statement piece for any modern farmhouse and luxe interior.

- A flawless choice for welcoming guests in an entryway or for providing light above a dining table or kitchen island
- Four elegant candelabra lights ornament the smooth frame
- The simple, sophisticated design is composed of an open, circular styling
- Four sleek, curved arms radiate down from the simple orb crowning the refined fixture
- Finished in bold Black and accented with painted antique nickel candelabra lights
- Clean, modern, open-cage design is ideal for modern farmhouse and luxe interiors
- Uses four 60-watt max candelabra base bulbs, or the LED equivalents, that are sold separately
- Measures 15 in diameter X 17-1/4 in height, Overall height with stem is 83-1/2 in, wire 180 in
- Progress Lighting products are designed for exceptional quality, reliability, and functionality

Category: Pendants

Finish: Black (Painted)

Construction: Steel Construction



Diameter: 15"

Height: 17-1/4"

Overall Ht. W/Chain And Stem: 83-1/2"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain mounted Mounting strap for outlet box included Six links of 9 gauge chain supplied One 6", four 12" lengths of stem included Canopy covers a standard 4" octagonal recessed outlet box 4.75" W., 0.75" ht., 4.75" depth	Pre-wired 15 feet of wire supplied 120 V	Quantity: Four 60w max. Candelabra Base E12 base Phenolic sockets	cULus Dry location listed