

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Incandescent

# P500164-143

## Gresham

A display of substantial style in an four-light foyer, Gresham Collection's frame was inspired by the elegance of traditional iron structures. Specific attention to forging details creates a distinctive collection for Transitional and Farmhouse interior spaces. Seeded glass shades and a Graphite finish pair together to complete the look.

- Graphite finishes and organic seeded-glass shades form the basis of this collection that channels traditional iron structures
- This four-light foyer fixture greets visitors with a pleasing, open feel within its dramatic dark frame
- The fixture feels most at home in a traditional or farmhouse-style setting
- With hand-forged details, the dark graphite base and seeded-glass shades make this chandelier a dramatic focal point
- Measures 20in diameter x 26 1/4in ht.
- Includes a cluster candelabra of 4 candelabra base lamps with seeded-glass shades
- Uses four, 60-watt max. candelabra base bulbs including LED equivalent (sold separately)
- Compatible with standard wall dimmer
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available



**Diameter: 20"**  
**Height: 26-1/4"**  
**Overall Ht. W/Chain: 100"**

Width: 3-1/8"  
Height: 5-7/8"

**Category:** Hall & Foyer

**Finish:** Graphite (painted)

**Construction:** Steel Construction

**Glass/Shade:** Clear Seeded glass Shades

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted  Mounting U-channel mounting bar for outlet box included  Six feet of 9 gauge chain supplied  Canopy covers a standard 4" octagonal recessed outlet box  5" W., 0.8125" ht., 5" depth	Pre-wired  15 feet of wire supplied  120 V	Quantity:  Four 60w max. Candelabra Base  E12 base phenolic sockets	cULus Dry location listed  1 year warranty