

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P500166-109

Carriage Hill

Featuring artful angles and soft metal tones, the Carriage Hill Collection offers a sophisticated three-light pendant design for Traditional interiors. A crisp fabric shade forms a hexagonal shape to surround an interior candelabra cluster in Brushed Bronze.

- This debonair three-light pendant is all about angles and curves, adding a jaunty look to your interiors
- A crisp, hexagonal linen shade gives studious accent to the sinuous brushed-metal frame
- These pendants make the best impact when displayed in libraries, home offices, entryways and foyers, breakfast nooks, or in groupings over a kitchen island
- Traditional interiors get a boost with the Carriage Hill pendants
- Elegant Brushed Bronze finish
- Measures 20 3/4in diameter x 24 1/2in ht.
- Uses three 60-watt max. candelabra bulbs including LED equivalent (sold separately)
- Compatible with standard wall dimmer
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available



Diameter: 20-3/4"
Height: 24-1/2"
Overall Ht. W/Chain: 99-1/2"

Category: Chandeliers

Finish: Brushed Bronze (plated)

Construction: Steel Construction

Glass/Shade: Ecru linen Shade

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|--|--|--|--|
| Ceiling mounted Mounting strap for outlet box included Six feet of 9 gauge chain supplied Canopy covers a standard 4" octagonal recessed outlet box 5.25" W., 1.25" ht., 5.25" depth | Pre-wired 15 feet of wire supplied 120 V | Quantity: Three 60w max. Candelabra Base E12 base phenolic sockets | cULus Dry location listed 1 year warranty |