

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P500196-081

Point Dume™ - Shearwater

The Shearwater hanging lanterns embody the love of easy coastal living. This lighter lantern option combine Antique Nickel with clear glass and a soft-beige stitched leather handle. This family of fixtures is part of Point Dume™ lighting collection which celebrates a curated mix of yesterday and today, distilling both industrial and artisanal influences.



Width: 16-1/4"
Height: 32"
Depth: 16-1/4"
Overall Ht. W/Chain: 109"

Category: Pendants

Finish: Antique Nickel (plated)

Construction: Steel Construction

Glass/Shade: Clear glass Flat Square/Rectangular

Glass

Width: 12"

Height: 6-3/4"

Glass 2

Width: 15-3/8"

Length: 0-3/16"

Height: 20-3/4"

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|---|--|---|---|
| Ceiling chain mounted Mounting strap for outlet box included Six feet of 9 gauge chain supplied Canopy covers a standard 4" octagonal recessed outlet box 5.875" W., 0.875" ht., 5.875" depth | Pre-wired 15 feet of wire supplied 120 V | Quantity: Four 60w max. Candelabra Base E12 base Phenolic sockets | cCSAus Dry location listed 1 year warranty |