

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P500198-160

Point Dume™ - Sandbar

Ageless Brushed Brass is layered in modern tiers for the Sandbar ceiling fixture, sconce and pendant light. The addition of tailormade leather details, brass hooks, milk glass and cables make for memorable, luxury lighting with infinite design applications. This family of fixtures is part of Point Dume™ lighting collection which celebrates a curated mix of yesterday and today, distilling both industrial and artisanal influences.



Diameter: 21-1/4"

Height: 14-7/8"

Overall Ht. W/Hooks and Chain: 93-1/2"

Glass

Width: 13-11/16"

Height: 12-3/16"

Category: Pendants

Finish: Brushed Brass (plated)

Construction: Steel Construction

Glass/Shade: Milk Glass glass Cylindrical

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted Mounting strap for outlet box included 60 in of 9 gauge chain supplied Canopy covers a standard 4" octagonal recessed outlet box 6" W., 1.1875" ht., 6" depth	Pre-wired 15 feet of wire supplied 120 V	Quantity: Three 100w max. Medium Base E26 base Porcelain sockets	cCSAus Dry location listed 1 year warranty