

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P500199-162 Point Dume™ - Surfrider

Like gentle waves lapping the sandy shore, the Surfrider pendant has tiers of metal curves converging in an ever-widening circle. Oversized hooks suspended from a simple orb surround a floating braided metal cable, beautifully marrying form and function for an industrial meets modern-minded point of view. This family of fixtures is part of the Point Dume™ lighting collection which celebrates a curated mix of yesterday and today, distilling both industrial and artisanal influences. Malibblue, a soft blue-gray finish inspired by the love of the Malibu waves and sky, one of three signature finishes developed especially for the Point Dume™ Collection.

- Tiers of metal overlap in a widening circle giving a triangular shape to the fixture, reminiscent of row upon row of gentle waves lapping the shoreline.
- Industrial details include a trio of oversized hooks surrounding the braided metal power cord and steel pinings attaching the rows of metal on the body of the fixture, allowing for the light source to subtly gleam between each row.
- Inspired by the weathered terrain of the Malibu, California coastline.
- Stunning Malibblue finish gleams in a soft blue-gray neutral tone reminiscent of the waves and sky.
- Hang in multiples over a kitchen island, a desk in a home office or try a pair on either side of a bed.
- Use singly or in multiples wherever task or accent lighting is needed.
- Surfrider works well across several style palettes.
- Coastal, with the inspiration of waves on the shore adding a calming and relaxed feeling to a room.
- Modern, as its clean, crisp lines fit well with minimalist décor.
- Urban Industrial, as the use of galvanized steel lends a sense of unfinished rawness adding an element of industrial chic to the room.
- Offered in Malibblue, a soft blue-gray finish inspired by the love of the Malibu waves and sky, one of three signature finishes developed especially for the Point Dume™ Collection.
- Inside tiers are finished in a gleaming white.
- Pendant with fixture diameter of 13-7/8 in. and height of 22-1/2 in.
- Chain adjustable, up to overall height 96-1/2 in.
- Use one 75w max. medium base incandescent or LED bulbs (bulbs not included).
- For an alternate look, try Edison bulbs or other vintage-style filament bulbs (bulbs not included).
- Ceiling chain mounted, the chain is adjustable as necessary for the space.



Diameter: 13-7/8 in  
Height: 22-1/2 in  
Overall Ht. W/Hooks and Chain: 96-1/2 in

**Category:** Pendants  
**Finish:** Malibblue (Plated)  
**Construction:** Steel Construction

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity: One 75 W max. Medium Base or LED equivalent	CCSAus Dry Location Listed
Mounting strap for outlet box included	15 feet of wire supplied	E26 base Porcelain socket	1-year Limited Warranty
48 in of 9 gauge chain supplied	120 V		
Canopy covers a standard 4" recessed outlet box: 6" W., 1.1875" ht., 6" depth			