

Project: Fixture Type: Location: Contact:

## P500315-009

## Kellwyn

Kellwyn Collection 4-Light Brushed Nickel Clear Glass Transitional Foyer Pendant Light

Category: Hall & Foyer Finish: Brushed Nickel (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Cylindrical



Length: 18 in Width: 18 in Height: 31-3/4 in

Overall Ht. W/Chain And Stem: 106-1/2 in

Clear Glass Cylindrical Width: 1-15/163 in

		Height: 7 in	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling/Stem + Chain	15 feet of wire supplied	Quantity: four 60 W max.	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 V	E12 base Phenolic Socket	1-year Limited Warranty
6 feet of 9 gauge chain supplied			
one 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 5.125" W., 0.875" ht., 5.125" depth			