

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P500357-31M

Saffert

Saffert Collection Three-Light New Traditional Matte Black White Linen Shade Pendant Light

Category: Pendants

Finish: Matte Black (Painted)

Construction: Steel Construction

Glass/Shade: White Linen Fabric Shade (Tapered), Diffuser Glass Disc



Diameter: 22 in
Height: 30 in
Overall Ht. W/Chain: 105 in

White Linen Fabric Shade (Tapered)
Width: 20-7/8 in
Height: 9-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(3) Medium Base (E26) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
6 feet of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5" W., 0.812" ht., 5" depth		Fully dimmable with dimmable bulbs	