

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P500359-109 Delayne

Delayne Collection One-Light Mid-Century Modern Brushed Bronze Etched Opal Glass Pendant Light

**Category:** Pendants

**Finish:** Brushed Bronze (Plated)

**Construction:** Steel Construction

**Glass/Shade:** Etched Opal Glass Globe



Diameter: 16-1/8 in  
Height: 21-5/8 in  
Overall Ht. W/Chain Or Stem: 85-1/2 in

Etched Opal Glass Globe  
Width: 14 in  
Height: 13 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
6 links of 9 Gauge chain supplied with quick link		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	
One 6", four 12" lengths of stem included		Fully dimmable with dimmable bulbs	
Canopy covers a standard 4" recessed outlet box: 5.18" W., 0.81" ht., 5.18" depth			