

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P500378-31M
Galloway

Category: Hall & Foyer
Finish: Matte Black (Painted) with Distressed White accent
Construction: Steel Construction



Diameter: 24 in
Height: 30-7/8 in
Overall Ht. W/Chain: 106-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	15 feet of wire supplied	(4) Candelabra Base (E12) Socket	cETLus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
6 feet of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth		Fully dimmable with dimmable bulbs	