PROGRESS LIGHTING

Project:		
Fixture Type:		

Location:

Contact:

P500381-31M Singleton

Category: Pendants Finish: Matte Black (Painted) Construction: Steel Construction Glass/Shade: Clear Glass Bowl



Diameter: 14 in Height: 8-1/2 in Overall Ht. W/Stem: 65 in

Clear Glass Bowl Width: 14 in Height: 5-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with Swivel	10 feet of wire supplied	(1) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
One 6", four 12" lengths of stem		Incandescent: 60-watt MAX per socket	
included plus 90-deg swivel for installation on sloped ceilings		LED: 12.5-watt MAX per socket	
Canopy covers a standard 4"		Fully dimmable with dimmable bulbs	
recessed outlet box: 4.87" W., 0.75" ht., 4.87" depth			