

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P5187-108

Uniquely shaped modern 10 inch pendant with sleek lines. This pendant utilizes an Oiled Rubbed Bronze finish with a white linen interior for optimal light output. This pendant is ideal for modern, transitional or urban industrial kitchens.

- Fun and flirty one-light metal shade mini-pendant.
- White gloss interior for optimal light output.
- Oil Rubbed Bronze finish.
- Includes two 6", one 12", two 15" stems and 6 links of chain.

Category: Pendants

Finish: Oil Rubbed Bronze (painted)

Construction: Steel Construction

Glass/Shade: Metal shade



Diameter: 10-1/8"
Height: 10-3/4"
Overall Ht. W/Stem: 77"

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|---|--|---|---|
| Ceiling stem hung with 6 links of chain mounted Mounting strap for outlet box included Six links of 9 gauge chain supplied Two 6", one 12", two 15" lengths of stem included Canopy covers a standard 4" octagonal recessed outlet box 4.9375" W., 1.125" ht., 4.9375" depth | Pre-wired 10 feet of wire supplied 120 V | Quantity: One 100w max. Medium Base E26 base ceramic socket | UL-CUL Dry location listed 1 year warranty |