



DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Halogen

P5238-31WB

Spread

Single-Light low voltage landscape spread light in a Black finish with a clear glass lens. 1/2 IP threaded adapter connector, mounting stake (P8618-31) and halogen lamp included. Units must be wired to a 12V transformer with proper capacity.

- Black finish.
- Tempered lens bottom.
- Top twists off for easy relamping.
- Units must be wired to an approved 12V transformer of proper capacity.

Diameter: 6-1/2"

Height: 13-1/16"

Glass

Width: 5-9/16"

Category: Landscape

Finish: Black (painted)

Construction: Aluminum construction

Glass/Shade: Clear glass lens

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|-----------------------|---|---|---|
| 1/2 IP thread mounted | Pre-wired 36" of wire supplied 12 V | Quantity: One 20w max. Halogen (G4, 12V)(included) G4 bi-pin base ceramic socket | cCSAus Wet location listed 1 year warranty |