

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____



Halogen

P5239-31WB

Flood Light

12V bi-pin die cast aluminum low voltage flood light with a specular aluminum reflector. Rotating strap mount with adjustment. Black powder coated to resist chipping and fading. Front hinged cover for easy relamping. Mounting ground stake (P8618-31) and connector included. Units must be wired to a 12V transformer with proper capacity.

- Black powder coat finish.
- Tempered glass cover.
- Units must be wired to an approved 12V transformer of proper capacity.
- Cover is locked with stainless steel screw.

Width: 5-9/16"
Height: 6-1/8"
13-15/16" with stake
Depth: 3-1/2"

Glass
Width: 5-3/16"
Height: 3-5/8"

Category: Landscape

Finish: Black (painted)

Construction: Die-cast aluminum construction

Glass/Shade: Tempered glass

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
In ground mounted	Pre-wired 36" of wire supplied 12 V	Quantity: One 50w max. Halogen (G4, 12V)(included) G4 bi-pin base ceramic socket	cCSAus Wet location listed 1 year warranty