

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Halogen

P5250-31

Ashmore

Inspired by lanterns from the Old World, the Ashmore low voltage landscape light incorporates handsome details, quill-scrolled arms and decorative finials. One-light path light in cast aluminum with water-seeded glass. Low voltage path light must be used with 12V transformer. Includes 1/2 IP threaded adapter, connector, mounting stake (P8618-31) and bulb.

- Textured Black finish with solid brass interior components.
- Water seeded glass curved panels.
- Quill-scrolled arms and decorative finials.
- Units must be wired to an approved 12V transformer of proper capacity.

Category: Landscape

Finish: Black (powdercoat)

Construction: Die-cast aluminum construction

Glass/Shade: Water seeded glass curved panels



Width: 6-1/4"

Height: 24"

Depth: 9-1/2"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
1/2 IP thread mounted	Pre-wired 6 feet of wire supplied 12 V	Quantity: One 18w max. T5 wedge base(included) Wedge base socket	cCSAus Wet location listed 1 year warranty