

Project:

Fixture Type:

Location:

Contact:

P540033-020

Gables

Gables Collection One-Light Antique Bronze and Clear Glass Transitional Style Outdoor Post Lantern with DURASHIELD

Category: Outdoor

Finish: Antique Bronze (Painted)

Construction: Injection-Molded Plastic Construction

Glass/Shade: Clear Glass Cylindrical



Diameter: 7-1/2 in Height: 16-3/4 in

Clear Glass Cylindrical Width: 5-7/8 in Height: 10-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Post mounted, fits standard 3" post (sold separately)	6 inches of wire supplied	(1) Medium Base (E26) Socket	cETLus Wet Location Listed
Post Mount	120 V	Lamp Type A19	5-year Limited Warranty
Post Mount covers a standard 4"		Incandescent: 75-watt MAX per socket	
recessed outlet box		LED: 15-watt MAX per socket	
		Dimmable to 10% brightness (See Dimming Notes)	