

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

**P540093-020**  
**Padgett**

Padgett Collection One-Light Transitional Antique Bronze Clear Seeded Glass  
Outdoor Post Light

**Category:** Outdoor  
**Finish:** Antique Bronze (Painted)  
**Construction:** Cast Aluminum Construction  
**Glass/Shade:** Clear Seeded Glass Panel



Square: 8 in  
Height: 18-1/2 in

Clear Seeded Glass Panel

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Post mounted, fits standard 3" post (sold separately)	6 inches of wire supplied  120 VAC	(1) Medium Base (E26) Socket  Lamp Type A19  Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket  Fully dimmable with dimmable bulbs	cCSAus Wet Location Listed  1-year Limited Warranty