

DATE:

NAME:

PROJECT:

Incandescent

P550027-031

TYPE:

Hermosa

Outdoor Mediterranean-style lanterns in the Hermosa family complement Transitional, Rustic Farmhouse and Modern Farmhouse exteriors. These large-scale pieces feature beautiful detail and a die cast aluminum frames. Wrought iron styling perfectly frames beautiful clear, water glass shades.

- Features Mediterranean-style design
- Complement Transitional, Rustic Farmhouse and Modern Farmhouse exteriors
- Textured Black finish
- Wrought iron styling perfectly frames beautiful clear, water glass shades
- Hanging lantern uses one 100 watt. max medium base lamp (sold separately)
- These large-scale pieces feature beautiful detail and a die cast aluminum frames
- Outdoor lanterns add illumination to walkways and pathways to enhance safety and security
- Suitable for a variety of exteriors

Category: Outdoor

Finish: Black (painted)

Construction: Aluminum

Glass/Shade: Clear Water Glass shade



Diameter: 12" Height: 26-1/2" Overall Ht. W/Chain: 101-1/2"

Glass Width: 6-1/2" Height: 14-3/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Hanging mounted	10 feet of wire supplied	Quantity:	cCSAus Damp location listed
Mounting strap for outlet box included Six feet of 9 gauge chain supplied	120 V	One 100w max. medium E26 base	1 year limited warranty
Canopy covers a standard 4" octagonal recessed outlet box 5" W., 0.875" ht., 5" depth			