

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P550031-031

Haslett

The one-light hanging lantern in the Haslett Collection features a design with intersecting linear details that surrounds clear seeded glass and finished in Black. Coastal-inspired frame is suitable to complement architecture with Farmhouse flair.

- Curving stems and linear banding joined with rivets conjure images of seaport locales
- The intersecting linear details surround clear seeded glass
- Haslett's design and construction is a good fit for Coastal, Farmhouse and Industrial-styled homes
- Sturdy Black finish
- Measures 7 1/2in diameter x 16 1/4in ht.
- Uses one medium base bulb, 100-watt max., and is perfectly compatible with a wide variety of bulbs including incandescent, LED, Vintage ST64 and more (all sold separately)
- UL Safety listed for use in damp locations
- Compatible with standard wall dimmer
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available



Diameter: 7-1/2"
Height: 16-1/4"
Overall Ht. W/Chain: 90"

Width: 4-3/8"
Height: 11-3/16"

Category: Outdoor

Finish: Black (painted)

Construction: Steel Construction

Glass/Shade: Clear Seeded glass Shade

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted Mounting strap for outlet box included Six feet of 9 gauge chain supplied Canopy covers a standard 4" octagonal recessed outlet box 4.75" W., 1" ht., 4.75" depth	Pre-wired 10 feet of wire supplied 120 V	Quantity: One 100w max. Medium Base E26 base porcelain socket	cULus Damp location listed 1 year warranty