

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

P550035-009

Burlington

The Burlington collection flush mount fixture features an aluminum construction, weather-resistant performance with clear, beveled glass panels. Suitable for both indoor and outdoor applications, the open bottom design allows easy access to replace light bulbs.

- Burlington is a 1-light outdoor flush mount fixture
- Burlington outdoor lanterns are suitable for Urban Industrial, Modern and Coastal exteriors
- Uses 1, 60-watt max. medium base bulb including LED equivalent (sold separately)
- Clear beveled glass
- Aluminum frame with Brushed Nickel finish
- Measures 7"W x 7"H
- Open bottom design allows easy access to replace lamps
- Outdoor lanterns

Category: Outdoor

Finish: Brushed Nickel (plated)

Construction: Aluminum construction

Glass/Shade: Clear Beveled Glass



Width: 7"

Height: 7"

Depth: 7"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted Mounting plate for outlet box included Unit covers a standard 4" octagonal recessed outlet box 7" W., 0.625" ht., 7" depth	Pre-wired 6" of wire supplied 120 V	Quantity: One 60w max. medium base E26 base Porcelain socket	cCSAus Damp location listed 1-year limited warranty