

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

# P550036-031

## New Haven

A Black finish complements clear, beveled glass in the New Haven outdoor lantern collection. Featuring an aluminum construction and clear, beveled glass panels, the flush mount fixture is suitable for Traditional indoor or outdoor settings. An open bottom design allows easy access to replace light bulbs.

- New Haven is a 2-light outdoor flush mount fixture
- New Haven outdoor lanterns are suitable for Traditional exteriors
- Uses 2, 60-watt max. medium base bulb including LED equivalent (sold separately)
- Clear beveled glass panels
- Aluminum frame
- Black finish
- Measures 11" W x 6" H
- Open bottom design allows easy access to replace lamps
- Outdoor lanterns add illumination to exterior spaces - such as patios or porches - to enhance safety and security, while enhancing curb appeal
- Damp location listed

**Category:** Outdoor

**Finish:** Black (painted)

**Construction:** Aluminum construction

**Glass/Shade:** Clear Beveled Glass Panel



**W: 11"**  
**Height: 6"**  
**Depth: 9-1/2"**

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted Mounting plate for outlet box included Unit covers a standard 4" octagonal recessed outlet box 11" W., 1" ht., 9.5" depth	Pre-wired 6" of wire supplied 120 V	Quantity: Two 60w max. medium base E26 base Porcelain sockets	cCSAus Damp location listed 1-year limited warranty