

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P550094-031 Tremont

Tremont Collection 1-Light Matte Black Clear Seeded Glass Farmhouse Semi-Flush Mount Ceiling Light

**Category:** Outdoor

**Finish:** Matte Black (Painted)

**Construction:** Steel Construction

**Glass/Shade:** Clear Seeded Glass Cylindrical



Length: 9 in  
Width: 9 in  
Height: 10 in

Clear Seeded Glass Cylindrical  
Width: 4-3/8 in  
Height: 7-9/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	6 inches of wire supplied	Quantity: one 60 W max.	cULus Damp Location Listed
Mounting plate for outlet box included	120 V	E26 base Porcelain Socket	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5.125" W., 5.125" ht., 1" depth			