

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Incandescent

# P5529-87

## Coventry

Capture the romance with this two-light hanging lantern from the Coventry collection that features optic hammered glass, stylized cap and Sheppard's hook. Die-cast aluminum construction. Fieldstone finish.

- Fieldstone finish.
- Optic hammered glass.
- Romantic style.

**Category:** Outdoor

**Finish:** Fieldstone (painted)

**Construction:** Die-cast aluminum Construction

**Glass/Shade:** Hammered glass



**Diameter:** 9-7/8"  
**Height:** 19"  
**Overall Ht. W/Chain:** 94"

Glass

Width: 7-7/16"

Height: 8.9688"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted  Mounting strap for outlet box included  Six feet of 9 gauge chain supplied  Canopy 4.5261" W., 0.9295" ht., 4.5261" depth	Pre-wired  10 feet of wire supplied  120 V	Quantity:  Two 60w max. Candelabra Base  E12 base sockets	UL-CUL Damp location listed  1 year warranty